


PRODUCT CONFIGURATIONS



EE-1135

Sanitary High-Lift Box/Container Dumper



flexicon®

USA

FLEXICON CORPORATION
Tel: 1 888 FLEXICON
(1 888 353 9426)
Tel: 1 610 814 2400
E-mail: sales@flexicon.com
Web: www.flexicon.com

UK

FLEXICON (EUROPE) LTD
Tel: +44 (0)1227 374710
E-mail: sales@flexicon.co.uk
Web: www.flexicon.co.uk

AUSTRALIA

FLEXICON CORPORATION
(AUSTRALIA) PTY LTD
Tel: +61 (0)7 3879 4180
E-mail: sales@flexicon.com.au
Web: www.flexicon.com.au

SOUTH AFRICA

FLEXICON AFRICA (PTY) LTD
Tel: +27 (0)41 453 1871
E-mail: sales@flexicon.co.za
Web: www.flexicon.co.za

SPAIN

FLEXICON EUROPE SPAIN S.L.
Tel: +34 930 020 509
E-mail: ventas@flexicon.es
Web: www.flexicon.es

FRANCE

FLEXICON (EUROPE) LTD
Tel: +33 (0)7 61 36 56 12
E-mail: ventes@flexicon.fr
Web: www.flexicon.fr

GERMANY

FLEXICON EUROPE GmbH
Tel: +49 173 900 78 76
E-mail: vertrieb@flexiconeurope.de
Web: www.flexicondeutschland.de

SINGAPORE

FLEXICON SINGAPORE PTE LTD
Tel: +65 6778 9225
E-mail: sales@flexicon.com.sg
Web: www.flexicon.com.sg

INDONESIA

FLEXICON SINGAPORE PTE LTD
Tel: +62 81 1103 2400
E-mail: sales@flexicon.co.id
Web: www.flexicon.co.id

MALAYSIA

FLEXICON SINGAPORE PTE LTD
Tel: +60 10 282 2400
E-mail: sales@flexicon.com.my
Web: www.flexicon.com.my

Sanitary High-Lift Box/Container Dumper

This sanitary TIP-TITE® High-Lift Box/Container Dumper from Flexicon discharges dust-free into vessels 6 to 10 ft (1830 to 3050 mm) above the plant floor.

Boxes and other containers are loaded at floor level and hydraulically seated against a discharge hood. The assembly is then hydraulically elevated and tipped, causing the discharge hood spout to seat against a gasketed receiving ring installed on any receiving vessel or process equipment. Opening of a pneumatically actuated slide gate valve at the spout outlet allows controlled, dust-free discharge, while closing it allows partially empty boxes and containers to be returned to the plant floor.

The unit accommodates Gaylords and other boxes from 36 to 48 in. (915 to 1220 mm) on a side and 39 to 44 in. (990 to 1117 mm) overall height.

Constructed of stainless steel finished to food, pharmaceutical or industrial standards, the unit is engineered to perform with fail-safe reliability under constant use in demanding environments.

It is also available constructed of carbon steel, and offered with optional receiving hoppers configured with the company's mechanical or pneumatic conveyors to transport discharged material to any plant location.



Container platform of sanitary TIP-TITE® High-Lift Box/Container Dumper raises to form dust-tight seal between container and discharge hood before the assembly is raised vertically and then tipped, mating the hood outlet with the gasketed inlet port on any receiving vessel 6 to 10 ft (1830 to 3050 mm) high.