


PRODUCT CONFIGURATIONS



V-1034

Sanitary Bulk Bag Filler Brings Fill Head to Operator



flexicon®

USA

FLEXICON CORPORATION
Tel: 1 888 FLEXICON
(1 888 353 9426)
Tel: 1 610 814 2400
E-mail: sales@flexicon.com
Web: www.flexicon.com

UK

FLEXICON (EUROPE) LTD
Tel: +44 (0)1227 374710
E-mail: sales@flexicon.co.uk
Web: www.flexicon.co.uk

AUSTRALIA

FLEXICON CORPORATION
(AUSTRALIA) PTY LTD
Tel: +61 (0)7 3879 4180
E-mail: sales@flexicon.com.au
Web: www.flexicon.com.au

SOUTH AFRICA

FLEXICON AFRICA (PTY) LTD
Tel: +27 (0)41 453 1871
E-mail: sales@flexicon.co.za
Web: www.flexicon.co.za

SPAIN

FLEXICON EUROPE SPAIN S.L.
Tel: +34 930 020 509
E-mail: ventas@flexicon.es
Web: www.flexicon.es

FRANCE

FLEXICON (EUROPE) LTD
Tel: +33 (0)7 61 36 56 12
E-mail: ventes@flexicon.fr
Web: www.flexicon.fr

GERMANY

FLEXICON EUROPE GmbH
Tel: +49 173 900 78 76
E-mail: vertrieb@flexiconeurope.de
Web: www.flexicondeutschland.de

SINGAPORE

FLEXICON SINGAPORE PTE LTD
Tel: +65 6778 9225
E-mail: sales@flexicon.com.sg
Web: www.flexicon.com.sg

INDONESIA

FLEXICON SINGAPORE PTE LTD
Tel: +62 81 1103 2400
E-mail: sales@flexicon.co.id
Web: www.flexicon.co.id

MALAYSIA

FLEXICON SINGAPORE PTE LTD
Tel: +60 10 282 2400
E-mail: sales@flexicon.com.my
Web: www.flexicon.com.my

Sanitary Bulk Bag Filler Brings Fill Head to Operator

Flexicon's bulk bag filler features all-stainless construction finished to sanitary standards, and a pivot-down fill head that enables the operator to connect empty bags at floor level and resume filling operations rapidly.

The SWING-DOWN® bulk bag filler simultaneously lowers and pivots the fill head, stopping it in a vertically oriented position that places the bag inlet spout inflatable connection, inflator button, and four bag loop latches within reach of an operator standing on the plant floor.

The new design significantly increases the safety and speed of connecting bulk bags by bringing the fill head to the operator in a vertical position at floor level. The connection points of a conventional filler are beyond the reach of most operators, even when bags as short as 4 ft (1220 mm) are being filled.

The new design eliminates the danger of stepping onto and over roller conveyors to access rear bag hooks and spout connection collars, and of standing on the conveyor and bending over with head and arms inserted beneath operational fill head components to pull bag spouts upward over inflatable collars while reaching for bag inflator buttons.

A remote console or wall-mounted panel houses controls to raise and pivot the fill head into a locked, horizontal "fill position," automatically inflate the bag to remove creases, open a flow control valve or start a feed device, and stop the flow of material once a preset fill weight has been gained. Optional vibratory decks de-aerate and densify material in the bag at preset set points to create a solid, stable bag, ready for shipment.

Once bags are filled, the controller deflates the spout connection collar, releases the loop latches, and raises the fill head to fully disengage the spout, enabling the bag to exit the filler automatically on an optional roller conveyor.

A patented mechanism automatically resets the latch after releasing the bag loops, and re-positions it as the fill head pivots into a vertical position, enabling the latch to receive bag loops inserted by an operator and to re-latch automatically.

The sanitary filler is intended for food, dairy and pharmaceutical applications requiring rapid, thorough wash down, as well as for chemical applications in which cross-contamination is a concern.

