


PRODUCT CONFIGURATIONS



W-0697

Sanitary Bag Dump Station



flexicon®

USA

FLEXICON CORPORATION
Tel: 1 888 FLEXICON
(1 888 353 9426)
Tel: 1 610 814 2400
E-mail: sales@flexicon.com
Web: www.flexicon.com

UK

FLEXICON (EUROPE) LTD
Tel: +44 (0)1227 374710
E-mail: sales@flexicon.co.uk
Web: www.flexicon.co.uk

AUSTRALIA

FLEXICON CORPORATION
(AUSTRALIA) PTY LTD
Tel: +61 (0)7 3879 4180
E-mail: sales@flexicon.com.au
Web: www.flexicon.com.au

SOUTH AFRICA

FLEXICON AFRICA (PTY) LTD
Tel: +27 (0)41 453 1871
E-mail: sales@flexicon.co.za
Web: www.flexicon.co.za

SPAIN

FLEXICON EUROPE SPAIN S.L.
Tel: +34 930 020 509
E-mail: ventas@flexicon.es
Web: www.flexicon.es

FRANCE

FLEXICON (EUROPE) LTD
Tel: +33 (0)7 61 36 56 12
E-mail: ventes@flexicon.fr
Web: www.flexicon.fr

GERMANY

FLEXICON EUROPE GmbH
Tel: +49 173 900 78 76
E-mail: vertrieb@flexiconeurope.de
Web: www.flexicondeutschland.de

SINGAPORE

FLEXICON SINGAPORE PTE LTD
Tel: +65 6778 9225
E-mail: sales@flexicon.com.sg
Web: www.flexicon.com.sg

INDONESIA

FLEXICON SINGAPORE PTE LTD
Tel: +62 81 1103 2400
E-mail: sales@flexicon.co.id
Web: www.flexicon.co.id

MALAYSIA

FLEXICON SINGAPORE PTE LTD
Tel: +60 10 282 2400
E-mail: sales@flexicon.com.my
Web: www.flexicon.com.my

Sanitary Bag Dump Station

Flexicon's Sanitary Bag Dump Station for pneumatic conveying systems collects dust created during manual dumping of bulk materials from bags, boxes, drums and other containers, and allows rapid, tool-free wash down.

Optional rocker arms support the hood assembly above the hopper rim, eliminating the need for operators to lift and remove the hood during cleaning and inspection.

Similarly, a stainless rotary airlock valve at the hopper discharge is equipped with integral support rails that allow the rotor assembly to separate from the valve body for sanitizing of all material contact surfaces, and to close securely in seconds, also without tools.

A high velocity vacuum fan draws airborne dust from the operator's atmosphere onto two cartridge filters. Automatic reverse-pulse filter cleaning allows continuous, efficient operation; timer activated solenoid valves release short blasts of compressed plant air inside cartridge filters causing dust build-up on the outer filter surfaces to fall into the hopper.

Filters are accessed easily by removing the interior baffle, and replaced rapidly using quick-disconnect fittings.

The all-stainless unit is also offered with an integral flexible screw conveyor, or with universal hopper discharge flange for connection to downstream process equipment, and is available mounted on frames with casters for in-plant mobility.

